# **TECHNICAL DATA SHEET**



# QSil 12 2 part encapsulation and potting silicone

**Property** 

Desc	

QSil 12 is a clear, transparent, low viscosity, two-component, liquid silicone material which cures at room temperature and is primarily intended for potting applications. This material is typically mixed at a ratio of 100:5. Once mixed, the material is self-leveling and will have a useful work-life of approximately two hours. The material will be fully cured after 24 – 48 hours at room temperature. This material can also be vulcanized at elevated temperatures (up to 70 °C) to increase the cure speed.

# **Key Features**

- Low viscosity
- · Variable cure speed with mild heat
- Transparency, room temperature cure
- · Good adhesion with use of a primer

#### Application

Protects against shock/vibration. Good deep section cure

#### **Use and Cure Information**

#### MIXING

QSil 12 should be catalyzed by weight with the appropriate amount of curing agent. The most commonly used curing agent concentration is 5% of QSil Cat 12. This concentration will provide a gel time of approximately 2 hours and a cure time of approximately 24 hours. Material should be mixed in a clean, compatible metal of plastic container. The volume of the container should be 4 – 5 times the volume of the material to be catalyzed. Thoroughly mix using clean tools, scraping the bottom and the side of the container to produce a homogeneous mixture.

#### **DE-AERATION**

Air trapped during mixing should be removed to eliminate voids in the cured product. Vacuum de-airing may be necessary to completely remove all entrapped air bubbles. To ensure proper de-airing, subject the mixed material to 29 inches of mercury. When using QSil 12 for potting, a de-aeration step may be necessary after pouring to avoid capturing air in complex assemblies.

# **BONDING**

QSil 12 silicone rubber compounds require the use of a primer to bond to a non-silicone surface. Thoroughly clean the substrate with a non-oily solvent such as naphtha or methyl ethyl ketone (MEK) and let dry. Then apply a uniform thin film of silicone primer and allow time to dry for one hour or more.

Uncured Product		
Color A		Clear slight haze
Color B		Clear, slight yellow
Cure Profile		72 hrs at room temperature
Cure Type		Condensation
Density A	BS ISO 2781	1.00

Test Method Value

Density B BS ISO 2781 **0.85**Gel Time at 25°C/77°F 60 - **180 min**Mix Ratio By Weight **20:1** 

Pot Life mins at 23°C/73°F 60 - 180 mins Rheology Liquid

Viscosity A Brookfield 1400 cP Viscosity B Brookfield 15 cP

# **Cured Product**

Color		Clear, to slightly hazy yellow
Density	BS ISO 2781	1.00 g/cm3
Elongation at Break	ISO 37	35 %
Hardness Shore A	ASTM D 2240-95	18
Linear Shrinkage (%)		1.00 %
Max Working Temp		204 °C / 399 °F
Min Working Temp		-55 °C / -67 °F
Tensile Strength	ISO 37	0.14 N/mm2 / 20 psi
Thermal Conductivity		0.18 W/mK
Electrical Properties		
Dielectric Constant	ASTM D-150	3.00
Dialoctric Ctropath (\//mil)		400 V/m:1

Dielectric Strength (V/mil)		400 V/mil
Dielectric Strength kV/mm	ASTM D-149	12.4 kV/mm / 315 V/mil
Dissipation Factor	ASTM D-150	0.001
Volume Resistivity (Ohms	ASTM D-257	1E+13 ohms cm

# Storage

Max Storage Temperature 38 °C / 100 °F Shelf Life 18 mths

UNCATALYZED		
TEST	QSil 12	QSil Cat 12
Appearance	Clear, slight haze	Clear, slight yellow
Viscosity	1,400 cps	15 cps
Specific Gravity	1.00	0.85
Solvent	None	Mineral Spirits

CATALYZED MIX RATIO 100:5 by weight (Base:Catalyst)		
Gel Time at 25 °C *	60 - 180 minutes	
Specific Gravity	1.00	
Durometer, Shore A, 24 hour	12	
Durometer, Shore A, 72 hour	18	
Useful Temperature Range	-55 °C = 204 °C	

<sup>\*</sup> Gel time is defined as the time required for the material to become a solid or a semi-solid.

# **Storage**

See product label and/or CoA for specific "Use By Date". Product should be stored in its original, unopened container Storage beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case, the properties required for the intended use should be checked for quality assurance reasons.

Revision Date 20 Oct 2021

Revision No 5

Download Date 21 Mar 2024